



SCL series



Vacuum suction cups

Flat suction cups (Ø 5 - 16 mm)




Reference	Material	D (mm)	Stroke (mm)	D1 (mm)	D2 (mm)	h	H	Connection	DN	Suitable fitting
SCL-F-5-0P5-C / P247G-X2	Chloroprene rubber (CR)	5	0.5	2	4.5	6	13.5			FL1-M-A-M5-1P5
SCL-F-7-1-C / P247H-X2	Chloroprene rubber (CR)	7	1.	2	5	6.5	14			FL1-M-A-M5-1P5
SCL-F-9-1P5-C / P247J-X2	Chloroprene rubber (CR)	9	1.5	2	5	7	14.5			FL1-M-A-M5-1P5
SCL-F-11-1-C / P247K-X2	Chloroprene rubber (CR)	11	1	3.8	9	10.5	19.5			FL1-M-A-M5-2P8
SCL-F-16P5-0P5-C / P247M-X2	Chloroprene rubber (CR)	16.5	0.5	3.8	8	11.5	20.5			FL1-M-A-M5-2P8
SCL-F-16P5-2-C / P247N-X2	Chloroprene rubber (CR)	16.5	2	3.8	9	11.5	20.5			FL1-M-A-M5-2P8
SCL-F-5-0P5-SI / P247P-X2	Silicone	5	0.5	2	4.5	6	13.5			FL1-M-A-M5-1P5
SCL-F-7-1-SI / P247Q-X2	Silicone	7	1	2	5	6.5	14			FL1-M-A-M5-1P5
SCL-F-9-1P5-SI / P247R-X2	Silicone	9	1.5	2	5	7	14.5			FL1-M-A-M5-1P5
SCL-F-11-1-SI / P247S-X2	Silicone	11	1	3.8	9	10.5	19.5			FL1-M-A-M5-2P8
SCL-F-16P5-0P5-SI	Silicone	16.5	0.5	3.8	8	11.5	20.5			FL1-M-A-M5-2P8
SCL-F-16P5-2-SI	Silicone	16.5	2	3.8	9	11.5	20.5			FL1-M-A-M5-2P8
SCL-F-5-0P5-C-M-M5	Chloroprene rubber (CR)	5	0.5	2	4.5	6	13.5	M5 (Male)	1.3	
SCL-F-7-1-C-M-M5	Chloroprene rubber (CR)	7	1.	2	5	6.5	14	M5 (Male)	1.3	
SCL-F-9-1P5-C-M-M5	Chloroprene rubber (CR)	9	1.5	2	5	7	14.5	M5 (Male)	1.3	
SCL-F-11-1-C-M-M5	Chloroprene rubber (CR)	11	1	3.8	9	10.5	19.5	M5 (Male)	2.8	
SCL-F-16P5-0P5-C-M-M5	Chloroprene rubber (CR)	16.5	0.5	3.8	8	11.5	20.5	M5 (Male)	2.8	
SCL-F-16P5-2-C-M-M5	Chloroprene rubber (CR)	16.5	2	3.8	9	11.5	20.5	M5 (Male)	2.8	
SCL-F-5-0P5-SI-M-M5	Silicone	5	0.5	2	4.5	6	13.5	M5 (Male)	1.3	
SCL-F-7-1-SI-M-M5	Silicone	7	1.	2	5	6.5	14	M5 (Male)	1.3	
SCL-F-9-1P5-SI-M-M5	Silicone	9	1.5	2	5	7	14.5	M5 (Male)	1.3	
SCL-F-11-1-SI-M-M5	Silicone	11	1	3.8	9	10.5	19.5	M5 (Male)	2.8	
SCL-F-16P5-0P5-SI-M-M5	Silicone	16.5	0.5	3.8	8	11.5	20.5	M5 (Male)	2.8	
SCL-F-16P5-2-SI-M-M5	Silicone	16.5	2	3.8	9	11.5	20.5	M5 (Male)	2.8	

Flat suction cups with support ribs (Ø 20 - 50 mm)





Reference	Material	D (mm)	Stroke (mm)	D1 (mm)	D2 (mm)	h (mm)	H (mm)	Connection	DN	Suitable fitting
SCL-F-22-0P5-C / P247T-X2	Chloroprene rubber (CR)	22	0.5	5.5	14.5	8	17.5			FL1-FM-A-M5-018G-3P1
SCL-F-22-2-C / P247U-X2	Chloroprene rubber (CR)	22	2.5	5.5	14.5	8	17.5			FL1-FM-A-M5-018G-3P1
SCL-F-28-1-C / P247V-X2	Chloroprene rubber (CR)	18	1	5.5	14.5	9	18.5			FL1-FM-A-M5-018G-3P1
SCL-F-32-2P5-C	Chloroprene rubber (CR)	32	2.5	5.5	14.5	10	19.5			FL1-FM-A-M5-018G-3P1
SCL-F-42-2-C	Chloroprene rubber (CR)	42	2	6.5	20	13	21			FL1-F-A-018G-5P2
SCL-F-53-2P5-C	Chloroprene rubber (CR)	53	2.5	10.5	27	17.5	26.5			FL1-F-A-018G-6P3
SCL-F-22-0P5-SI	Silicone	22	0.5	5.5	14.5	8	17.5			FL1-FM-A-M5-018G-3P1
SCL-F-22-2-SI	Silicone	22	2.5	5.5	14.5	8	17.5			FL1-FM-A-M5-018G-3P1
SCL-F-28-1-SI	Silicone	18	1	5.5	14.5	9	18.5			FL1-FM-A-M5-018G-3P1
SCL-F-32-2P5-SI	Silicone	32	2.5	5.5	14.5	10	19.5			FL1-FM-A-M5-018G-3P1
SCL-F-42-2-SI	Silicone	42	2	6.5	20	13	21			FL1-F-A-018G-5P2
SCL-F-53-2P5-SI	Silicone	53	2.5	10.5	27	17.5	26.5			FL1-F-A-018G-6P3
SCL-F-22-0P5-C-MF-M5-018	Chloroprene rubber (CR)	22	0.5	5.5	14.5	8	17.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-F-22-2-C-MF-M5-018	Chloroprene rubber (CR)	22	2.5	5.5	14.5	8	17.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-F-28-1-C-MF-M5-018	Chloroprene rubber (CR)	18	1	5.5	14.5	9	18.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-F-32-2P5-C-MF-M5-018	Chloroprene rubber (CR)	32	2.5	5.5	14.5	10	19.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-F-42-2-C-M-018	Chloroprene rubber (CR)	42	2	6.5	20	13	21	G 1/8 inch (Female)	5.2	
SCL-F-53-2P5-C-M-018	Chloroprene rubber (CR)	53	2.5	10.5	27	17.5	26.5	G 1/8 inch (Female)	6.3	
SCL-F-22-0P5-SI-MF-M5-018	Silicone	22	0.5	5.5	14.5	8	17.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-F-22-2-SI-MF-M5-018	Silicone	22	2.5	5.5	14.5	8	17.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-F-28-1-SI-MF-M5-018	Silicone	18	1	5.5	14.5	9	18.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-F-32-2P5-SI-MF-M5-018	Silicone	32	2.5	5.5	14.5	10	19.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-F-42-2-SI-M-018	Silicone	42	2	6.5	20	13	21	G 1/8 inch (Female)	5.2	
SCL-F-53-2P5-SI-M-018	Silicone	53	2.5	10.5	27	17.5	26.5	G 1/8 inch (Female)	6.3	

Flat suction cups with support ribs, complete with holders (Ø 20 - 50 mm)





Reference	Material	D (mm)	Stroke (mm)	H (mm)	Connection	DN
SCL-F-22-0P5-C-MF-M5-018-S	Chloroprene rubber (CR)	22	0.5	16	M5 (Female), G 1/8 inch (Male)	4.3
SCL-F-28-1-C-MF-M5-018-S	Chloroprene rubber (CR)	28	1	17	M5 (Female), G 1/8 inch (Male)	4.3
SCL-F-32-2P5-C-MF-M5-018-S	Chloroprene rubber (CR)	32	2.5	18	M5 (Female), G 1/8 inch (Male)	4.3
SCL-F-42-2-C-M-018-S	Chloroprene rubber (CR)	42	2	21	G 1/8 inch (Female)	6
SCL-F-53-2P5-C-M-018-S	Chloroprene rubber (CR)	53	2.5	26	G 1/8 inch (Female)	8.8
SCL-F-22-0P5-SI-MF-M5-018-S	Silicone	22	0.5	16	M5 (Female), G 1/8 inch (Male)	4.3
SCL-F-28-1-SI-MF-M5-018-S	Silicone	28	1	17	M5 (Female), G 1/8 inch (Male)	4.3
SCL-F-32-2P5-SI-MF-M5-018-S	Silicone	32	2.5	18	M5 (Female), G 1/8 inch (Male)	4.3
SCL-F-42-2-SI-M-018-S	Silicone	42	2	21	G 1/8 inch (Female)	6
SCL-F-53-2P5-SI-M-018-S	Silicone	53	2.5	26	G 1/8 inch (Female)	8.8

Bellows suction pad, 1.5 folds (Ø 6 - 16 mm)





Reference	Material	D (mm)	Stroke (mm)	D1 (mm)	D2 (mm)	D3 (mm)	h (mm)	H (mm)	Connection	DN	Suitable fitting
SCL-B-6-2-C / P247W-X2	Chloroprene rubber (CR)	6	2	2	4.5	2.2	9	16.5			FL1-M-A-M5-1P3
SCL-B-9-3P5-C / P247X-X2	Chloroprene rubber (CR)	9	3.5	2	5.5	3.8	12	19.5			FL1-M-A-M5-1P3
SCL-B-11-5-C / P247Y-X2	Chloroprene rubber (CR)	11	5	4	9	6	17	26.5			FL1-M-A-M5-2P8
SCL-B-16-7-C / P247Z-X2	Chloroprene rubber (CR)	16	7	4	9	8	19	28.5			FL1-M-A-M5-2P8
SCL-B-6-2-SI / P2482-X2	Silicone	6	2	2	4.5	2.2	9	16.5			FL1-M-A-M5-1P3
SCL-B-9-3P5-SI	Silicone	9	3.5	2	5.5	3.8	12	19.5			FL1-M-A-M5-1P3
SCL-B-11-5-SI / P2483-X2	Silicone	11	5	4	9	6	17	26.5			FL1-M-A-M5-2P8
SCL-B-16-7-SI / P2484-X2	Silicone	16	7	4	9	8	19	28.5			FL1-M-A-M5-2P8
SCL-B-6-2-C-M-M5	Chloroprene rubber (CR)	6	2	2	4.5	2.2	9	16.5	M5 (Male)	1.3	
SCL-B-9-3P5-C-M-M5	Chloroprene rubber (CR)	9	3.5	2	5.5	3.8	12	19.5	M5 (Male)	1.3	
SCL-B-11-5-C-M-M5	Chloroprene rubber (CR)	11	5	4	9	6	17	26.5	M5 (Male)	2.8	
SCL-B-16-7-C-M-M5	Chloroprene rubber (CR)	16	7	4	9	8	19	28.5	M5 (Male)	2.8	
SCL-B-6-2-SI-M-M5	Silicone	6	2	2	4.5	2.2	9	16.5	M5 (Male)	1.3	
SCL-B-9-3P5-SI-M-M5	Silicone	9	3.5	2	5.5	3.8	12	19.5	M5 (Male)	1.3	
SCL-B-11-5-SI-M-M5	Silicone	11	5	4	9	6	17	26.5	M5 (Male)	2.8	
SCL-B-16-7-SI-M-M5	Silicone	16	7	4	9	8	19	28.5	M5 (Male)	2.8	

Bellows suction pad, 1.5 folds (Ø 20 - 50 mm)




Reference	Material	D (mm)	Stroke (mm)	D1 (mm)	D2 (mm)	D3 (mm)	h (mm)	H (mm)	Connection	DN	Suitable fitting
SCL-B-20-9-C / P2485-X2	Chloroprene rubber (CR)	20	9	5.5	14.5	11	20	29.5			FL1-FM-A-M5-018G-3P1
SCL-B-32-9-C	Chloroprene rubber (CR)	32	9	5.5	14.5	17	26	35.6			FL1-FM-A-M5-018G-3P1
SCL-B-42-9-C	Chloroprene rubber (CR)	42	9	6.5	20	24	28	36			FL1-F-A-018G-5P2
SCL-B-52-12-C	Chloroprene rubber (CR)	52	12	10.5	27	31	35	44			FL1-F-A-018G-6P3
SCL-B-20-9-SI	Silicone	20	9	5.5	14.5	11	20	29.5			FL1-FM-A-M5-018G-3P1
SCL-B-32-9-SI	Silicone	32	9	5.5	14.5	17	26	35.6			FL1-FM-A-M5-018G-3P1
SCL-B-42-9-SI	Silicone	42	9	6.5	20	24	28	36			FL1-F-A-018G-5P2
SCL-B-52-12-SI	Silicone	52	12	10.5	27	31	35	44			FL1-F-A-018G-6P3
SCL-B-20-9-C-MF-M5-018	Chloroprene rubber (CR)	20	9	5.5	14.5	11	20	29.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-B-32-9-C-MF-M5-018	Chloroprene rubber (CR)	32	9	5.5	14.5	17	26	35.6	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-B-42-9-C-M-018	Chloroprene rubber (CR)	42	9	6.5	20	24	28	36	G 1/8 inch (Female)	5.2	
SCL-B-52-12-C-M-018	Chloroprene rubber (CR)	52	12	10.5	27	31	35	44	G 1/8 inch (Female)	6.3	
SCL-B-20-9-SI-MF-M5-018	Silicone	20	9	5.5	14.5	11	20	29.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-B-32-9-SI-MF-M5-018	Silicone	32	9	5.5	14.5	17	26	35.6	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-B-42-9-SI-M-018	Silicone	42	9	6.5	20	24	28	36	G 1/8 inch (Female)	5.2	
SCL-B-52-12-SI-M-018	Silicone	52	12	10.5	27	31	35	44	G 1/8 inch (Female)	6.3	

Bellows suction pad, 4.5 folds (Ø 20 - 50 mm)



Reference	Material	D (mm)	Stroke (mm)	D1 (mm)	D2 (mm)	D3 (mm)	h (mm)	H (mm)	Connection	DN	Suitable fitting
SCL-B-20-16-C	Chloroprene rubber (CR)	20	16	5	14.5	14	23	32.5			FL1-FM-A-M5-018G-3P1
SCL-B-30-21-C	Chloroprene rubber (CR)	30	21	6.5	20	21	32	32			FL1-F-A-018G-5P2
SCL-B-40-20-C	Chloroprene rubber (CR)	40	20	6.5	20	28	42	42			FL1-F-A-018G-5P2
SCL-B-50-30-C	Chloroprene rubber (CR)	50	30	10.5	27	35	51	51			FL1-F-A-018G-6P3
SCL-B-20-16-SI	Silicone	20	16	5	14.5	14	23	32.5			FL1-FM-A-M5-018G-3P1
SCL-B-30-21-SI	Silicone	30	21	6.5	20	21	32	32			FL1-F-A-018G-5P2
SCL-B-40-20-SI	Silicone	40	20	6.5	20	28	42	42			FL1-F-A-018G-5P2
SCL-B-50-30-SI	Silicone	50	30	10.5	27	35	51	51			FL1-F-A-018G-6P3
SCL-B-20-16-C-MF-M5-018	Chloroprene rubber (CR)	20	16	5	14.5	14	23	32.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-B-30-21-C-M-018	Chloroprene rubber (CR)	30	21	6.5	20	21	32	32	G 1/8 inch (Female)	3.1	
SCL-B-40-20-C-M-018	Chloroprene rubber (CR)	40	20	6.5	20	28	42	42	G 1/8 inch (Female)	5.2	
SCL-B-50-30-C-M-018	Chloroprene rubber (CR)	50	30	10.5	27	35	51	51	G 1/8 inch (Female)	6.2	
SCL-B-20-16-SI-MF-M5-018	Silicone	20	16	5	14.5	14	23	32.5	M5 (Female), G 1/8 inch (Male)	3.1	
SCL-B-30-21-SI-M-018	Silicone	30	21	6.5	20	21	32	32	G 1/8 inch (Female)	3.1	
SCL-B-40-20-SI-M-018	Silicone	40	20	6.5	20	28	42	42	G 1/8 inch (Female)	5.2	
SCL-B-50-30-SI-M-018	Silicone	50	30	10.5	27	35	51	51	G 1/8 inch (Female)	6.2	

Flat suction cups with standard lips and vulcanized holders, Ø 30 - 225 mm





Reference	Material	D (mm)	Stroke (mm)	D2 (mm)	D3 (mm)	h (mm)	H (mm)	h1 (mm)	h2 (mm)	A (mm)	B (mm)	Connection	DN
SCL-F-30-2P5-C-F-M5	Chloroprene rubber (CR)	30	2.5	10	18	10	17	3.5	2.5			M5 (Female)	3.2
SCL-F-50-4-C-F-018	Chloroprene rubber (CR)	50	4	18	33	11	18	5.5	4.5			G 1/8 inch (Female)	8.8
SCL-F-75-5-C-F-014	Chloroprene rubber (CR)	75	5.5	22	50	15	23	7	5.5			G 1/4 inch (Female)	11.8
SCL-F-100-10-N-F-038	NBR (nitrile rubber)	100	10	30	68	20	30	15.5	9.5			G 3/8 inch (Female)	15.2
SCL-F-150-10-C-F-012	Chloroprene rubber (CR)	150	10	35	100	26	42	12	9	30	G 1/8 inch	G 1/2 inch (Female)	19
SCL-F-225-8-C-F-034	Chloroprene rubber (CR)	225	8	50	150	34	54	14	11	50	G 1/8 inch	G 3/4 inch (Female)	24.5
SCL-F-30-2P5-SI-F-M5	Silicone	30	2.5	10	18	10	17	3.5	2.5			M5 (Female)	3.2
SCL-F-50-4-SI-F-018	Silicone	50	4	18	33	11	18	5.5	4.5			G 1/8 inch (Female)	8.8
SCL-F-75-5-SI-F-014	Silicone	75	5.5	22	50	15	23	7	5.5			G 1/4 inch (Female)	11.8
SCL-F-100-10-SI-F-038	Silicone	100	10	30	68	20	30	15.5	9.5			G 3/8 inch (Female)	15.2
SCL-F-150-10-SI-F-012	Silicone	150	10	35	100	26	42	12	9	30	G 1/8 inch	G 1/2 inch (Female)	19
SCL-F-225-8-SI-F-034	Silicone	225	8	50	150	34	54	14	11	50	G 1/8 inch	G 3/4 inch (Female)	24.5

Flat suction cups with robust lips and vulcanized holders, Ø 60 - 95 mm





Reference	Material	D (mm)	Stroke (mm)	D2 (mm)	H (mm)	h1 (mm)	Connection	DN
SCL-F-60-5-N-F-014	NBR (nitrile rubber)	60	5	38.5	16	5	G 1/4 inch (Female)	11.8
SCL-F-80-6-N-F-014	NBR (nitrile rubber)	80	6	53	18	6	G 1/4 inch (Female)	11.8
SCL-F-95-6-N-F-014	NBR (nitrile rubber)	95	6	68	19	6	G 1/4 inch (Female)	11.8
SCL-F-60-5-SI-F-014	Silicone	60	5	38.5	16	5	G 1/4 inch (Female)	11.8
SCL-F-80-6-SI-F-014	Silicone	80	6	53	18	6	G 1/4 inch (Female)	11.8
SCL-F-95-6-SI-F-014	Silicone	95	6	68	19	6	G 1/4 inch (Female)	11.8

Flat suction cups with very fine lips, Ø 40 - 200 mm





Reference	Material	D (mm)	Stroke (mm)	D3 (mm)	D4 (mm)	h (mm)	H (mm)	h3 (mm)	h4 (mm)	Color	Connection	DN
SCL-F-40-3-SI-F-018	Silicone	40	3	26	17	12.5	12.5	6	3	Clear	G 1/8 inch (Female)	8.5
SCL-F-40-3-NRE-F-018	NRE	40	3	26	17	12.5	12.5	6	3	Brown	G 1/8 inch (Female)	8.5
SCL-F-70-6-S-F-014	SBR	70	6	50	32.5	30	32	18	4	Reddish brown	G 1/4 inch (Female)	11.8
SCL-F-70-6-SI-F-014	Silicone	70	6	50	32.5	30	32	18	4	Clear	G 1/4 inch (Female)	11.8
SCL-F-70-6-NR-F-014	NR (natural rubber)	70	6	50	32.5	30	32	18	4	Beige	G 1/4 inch (Female)	11.8
SCL-F-70-6-NRE-F-014	NRE	70	6	50	32.5	30	32	18	4	Brown	G 1/4 inch (Female)	11.8
SCL-F-100-6-S-F-014	SBR	100	5	70	50.5	32	33	19	5	Reddish brown	G 1/4 inch (Female)	11.8
SCL-F-100-6-N-F-014	NBR (nitrile rubber)	100	5	70	50.5	32	33	19	5	Grey	G 1/4 inch (Female)	11.8
SCL-F-100-6-NR-F-014	NR (natural rubber)	100	5	70	50.5	32	33	19	5	Beige	G 1/4 inch (Female)	11.8
SCL-F-200-5-NRE-F-012	NRE	200	5	170	148	32	34	18	5	White	G 1/2 inch (Female)	19

Bellows suction pad, 2.5 folds, Ø 10 - 40 mm



Reference	Material	D (mm)	Stroke (mm)	D1 (mm)	D2 (mm)	D3 (mm)	h (mm)	H (mm)	Connection	DN	Suitable fitting
SCL-B-9-2-N / P2486-X2	NBR (nitrile rubber)	9	2	5	9	4	15	27.5			FL1-F-A-018G-3P3, FL1-M-A-018G-4
SCL-B-14-10-N / P2487-X2	NBR (nitrile rubber)	14	10	5	12	6	23	35			FL1-F-A-018G-3P3, FL1-M-A-018G-4
SCL-B-18-8-N / P2488-X2	NBR (nitrile rubber)	18	8	5	12	7	22	34			FL1-F-A-018G-3P3, FL1-M-A-018G-4
SCL-B-30-13-N	NBR (nitrile rubber)	30	13	8	19	12	33	48			FL1-F-A-014G-4, FL1-M-A-014G-4
SCL-B-40-20-N	NBR (nitrile rubber)	40	20	8	19	18	45	60			FL1-F-A-014G-4, FL1-M-A-014G-4
SCL-B-10-4-SI / P2489-X2	Silicone	10	4	5	10	6	14	26.5			FL1-F-A-018G-3P3, FL1-M-A-018G-4
SCL-B-14-10-SI	Silicone	14	10	5	12	6	23	35			FL1-F-A-018G-3P3, FL1-M-A-018G-4
SCL-B-18-8-SI	Silicone	18	8	5	12	7	22	34			FL1-F-A-018G-3P3, FL1-M-A-018G-4
SCL-B-30-13-SI	Silicone	30	13	8	19	12	33	48			FL1-F-A-014G-4, FL1-M-A-014G-4
SCL-B-40-20-SI-RED	Silicone	40	20	8	19	18	45	60			FL1-F-A-014G-4, FL1-M-A-014G-4
SCL-B-14-10-U	Polyurethane (PUR)	14	10	5	12	6	23	35			FL1-F-A-018G-3P3, FL1-M-A-018G-4
SCL-B-18-8-U	Polyurethane (PUR)	18	8	5	12	7	22	34			FL1-F-A-018G-3P3, FL1-M-A-018G-4
SCL-B-30-13-U	Polyurethane (PUR)	30	13	8	19	12	33	48			FL1-F-A-014G-4, FL1-M-A-014G-4
SCL-B-40-20-U	Polyurethane (PUR)	40	20	8	19	18	45	60			FL1-F-A-014G-4, FL1-M-A-014G-4
SCL-B-9-2-N-F-018	NBR (nitrile rubber)	9	2	5	9	4	15	27.5	G 1/8 inch (Female)	4	
SCL-B-14-10-N-F-018	NBR (nitrile rubber)	14	10	5	12	6	23	35	G 1/8 inch (Female)	4	
SCL-B-18-8-N-F-018	NBR (nitrile rubber)	18	8	5	12	7	22	34	G 1/8 inch (Female)	4	
SCL-B-30-13-N-F-014	NBR (nitrile rubber)	30	13	8	19	12	33	48	G 1/4 inch (Female)	4	
SCL-B-40-20-N-F-014	NBR (nitrile rubber)	40	20	8	19	18	45	60	G 1/4 inch (Female)	4	
SCL-B-10-4-SI-F-018	Silicone	10	4	5	10	6	14	26.5	G 1/8 inch (Female)	4	
SCL-B-14-10-SI-F-018	Silicone	14	10	5	12	6	23	35	G 1/8 inch (Female)	4	
SCL-B-18-8-SI-F-018	Silicone	18	8	5	12	7	22	34	G 1/8 inch (Female)	4	
SCL-B-30-13-SI-F-014	Silicone	30	13	8	19	12	33	48	G 1/4 inch (Female)	4	
SCL-B-40-20-SI-F-014	Silicone	40	20	8	19	18	45	60	G 1/4 inch (Female)	4	
SCL-B-14-10-U-F-018	Polyurethane (PUR)	14	10	5	12	6	23	35	G 1/8 inch (Female)	4	
SCL-B-18-8-U-F-018	Polyurethane (PUR)	18	8	5	12	7	22	34	G 1/8 inch (Female)	4	
SCL-B-30-13-U-F-014	Polyurethane (PUR)	30	13	8	19	12	33	48	G 1/4 inch (Female)	4	
SCL-B-40-20-U-F-014	Polyurethane (PUR)	40	20	8	19	18	45	60	G 1/4 inch (Female)	4	
SCL-B-9-2-N-M-018	NBR (nitrile rubber)	9	2	5	9	4	15	27.5	G 1/8 inch (Male)	4	
SCL-B-14-10-N-M-018	NBR (nitrile rubber)	14	10	5	12	6	23	35	G 1/8 inch (Male)	4	
SCL-B-18-8-N-M-018	NBR (nitrile rubber)	18	8	5	12	7	22	34	G 1/8 inch (Male)	4	
SCL-B-30-13-N-M-014	NBR (nitrile rubber)	30	13	8	19	12	33	48	G 1/4 inch (Male)	4	
SCL-B-40-20-N-M-014	NBR (nitrile rubber)	40	20	8	19	18	45	60	G 1/4 inch (Male)	4	
SCL-B-10-4-SI-M-018	Silicone	10	4	5	10	6	14	26.5	G 1/8 inch (Male)	4	
SCL-B-14-10-SI-M-018	Silicone	14	10	5	12	6	23	35	G 1/8 inch (Male)	4	
SCL-B-18-8-SI-M-018	Silicone	18	8	5	12	7	22	34	G 1/8 inch (Male)	4	
SCL-B-30-13-SI-M-014	Silicone	30	13	8	19	12	33	48	G 1/4 inch (Male)	4	
SCL-B-40-20-SI-M-014	Silicone	40	20	8	19	18	45	60	G 1/4 inch (Male)	4	
SCL-B-14-10-U-M-018	Polyurethane (PUR)	14	10	5	12	6	23	35	G 1/8 inch (Male)	4	
SCL-B-18-8-U-M-018	Polyurethane (PUR)	18	8	5	12	7	22	34	G 1/8 inch (Male)	4	
SCL-B-30-13-U-M-014	Polyurethane (PUR)	30	13	8	19	12	33	48	G 1/4 inch (Male)	4	
SCL-B-40-20-U-M-014	Polyurethane (PUR)	40	20	8	19	18	45	60	G 1/4 inch (Male)	4	



Oval-flat suction cup, 15 - 100 mm



Reference	Material	AxB (mm)	Stroke (mm)	D1 (mm)	D2 (mm)	D3 (mm)	h (mm)	H (mm)	Connection	DN	Suitable fitting
SCL-OF-15-1-N	NBR (nitrile rubber)	15x5	1	5	9	2	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-18-1-N	NBR (nitrile rubber)	18x6	1	5	9	2	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-24-1-N	NBR (nitrile rubber)	24x8	1	5	12	3	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-30-2-N	NBR (nitrile rubber)	30x10	2	5	12	3.5	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-36-2-N	NBR (nitrile rubber)	36x12	2	5	12	4.5	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-45-3-N	NBR (nitrile rubber)	45x15	3	12	17	4	21	33			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OF-60-3-N	NBR (nitrile rubber)	60x20	3	12	17	4	21	33			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OF-75-3-N	NBR (nitrile rubber)	75x25	3	12	18	4	22	34			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OF-100-3-N	NBR (nitrile rubber)	100x35	3	12	18	7.5	22	34			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OF-15-1-SI	Silicone	15x5	1	5	9	2	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-18-1-SI	Silicone	18x6	1	5	9	2	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-24-1-SI	Silicone	24x8	1	5	12	3	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-30-2-SI	Silicone	30x10	2	5	12	3.5	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-36-2-SI	Silicone	36x12	2	5	12	4.5	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-45-3-SI	Silicone	45x15	3	12	17	4	21	33			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OF-60-3-SI	Silicone	60x20	3	12	17	4	21	33			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OF-75-3-SI	Silicone	75x25	3	12	18	4	22	34			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OF-18-1-U	Polyurethane (PUR)	18x6	1	5	9	2	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-24-1-U	Polyurethane (PUR)	24x8	1	5	12	3	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-30-2-U	Polyurethane (PUR)	30x10	2	5	12	3.5	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-36-2-U	Polyurethane (PUR)	36x12	2	5	12	4.5	12	22			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OF-45-3-U	Polyurethane (PUR)	45x15	3	12	17	4	21	33			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OF-60-3-U	Polyurethane (PUR)	60x20	3	12	17	4	21	33			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OF-15-1-N-F-018	NBR (nitrile rubber)	15x5	1	5	9	2	12	22	G 1/8 inch (Female)	3	
SCL-OF-18-1-N-F-018	NBR (nitrile rubber)	18x6	1	5	9	2	12	22	G 1/8 inch (Female)	3	
SCL-OF-24-1-N-F-018	NBR (nitrile rubber)	24x8	1	5	12	3	12	22	G 1/8 inch (Female)	3	
SCL-OF-30-2-N-F-018	NBR (nitrile rubber)	30x10	2	5	12	3.5	12	22	G 1/8 inch (Female)	3	
SCL-OF-36-2-N-F-018	NBR (nitrile rubber)	36x12	2	5	12	4.5	12	22	G 1/8 inch (Female)	3	
SCL-OF-15-1-N-M-018	NBR (nitrile rubber)	15x5	1	5	9	2	12	26	G 1/8 inch (Male)	3	
SCL-OF-18-1-N-M-018	NBR (nitrile rubber)	18x6	1	5	9	2	12	26	G 1/8 inch (Male)	3	

SCL-OF-24-1-N-M-018	NBR (nitrile rubber)	24x8	1	5	12	3	12	26	G 1/8 inch (Male)	3
SCL-OF-30-2-N-M-018	NBR (nitrile rubber)	30x10	2	5	12	3.5	12	26	G 1/8 inch (Male)	3
SCL-OF-36-2-N-M-018	NBR (nitrile rubber)	36x12	2	5	12	4.5	12	26	G 1/8 inch (Male)	3
SCL-OF-15-1-N-M-M5	NBR (nitrile rubber)	15x5	1	5	9	2	12	22	G M5 (Male)	2.4
SCL-OF-18-1-N-M-M5	NBR (nitrile rubber)	18x6	1	5	9	2	12	22	G M5 (Male)	2.4
SCL-OF-24-1-N-M-M5	NBR (nitrile rubber)	24x8	1	5	12	3	12	22	G M5 (Male)	2.4
SCL-OF-30-2-N-M-M5	NBR (nitrile rubber)	30x10	2	5	12	3.5	12	22	G M5 (Male)	2.4
SCL-OF-36-2-N-M-M5	NBR (nitrile rubber)	36x12	2	5	12	4.5	12	22	G M5 (Male)	2.4
SCL-OF-45-3-N-F-014	NBR (nitrile rubber)	45x15	3	12	17	4	21	33	G 1/4 inch (Female)	6.5
SCL-OF-60-3-N-F-014	NBR (nitrile rubber)	60x20	3	12	17	4	21	33	G 1/4 inch (Female)	6.5
SCL-OF-75-3-N-F-014	NBR (nitrile rubber)	75x25	3	12	18	4	22	34	G 1/4 inch (Female)	6.5
SCL-OF-100-3-N-F-014	NBR (nitrile rubber)	100x35	3	12	18	7.5	22	34	G 1/4 inch (Female)	6.5
SCL-OF-45-3-N-M-014	NBR (nitrile rubber)	45x15	3	12	17	4	21	37	G 1/4 inch (Male)	6.5
SCL-OF-60-3-N-M-014	NBR (nitrile rubber)	60x20	3	12	17	4	21	37	G 1/4 inch (Male)	6.5
SCL-OF-75-3-N-M-014	NBR (nitrile rubber)	75x25	3	12	18	4	22	38	G 1/4 inch (Male)	6.5
SCL-OF-100-3-N-M-014	NBR (nitrile rubber)	100x35	3	12	18	7.5	22	38	G 1/4 inch (Male)	6.5
SCL-OF-15-1-SI-F-018	Silicone	15x5	1	5	9	2	12	22	G 1/8 inch (Female)	3
SCL-OF-18-1-SI-F-018	Silicone	18x6	1	5	9	2	12	22	G 1/8 inch (Female)	3
SCL-OF-24-1-SI-F-018	Silicone	24x8	1	5	12	3	12	22	G 1/8 inch (Female)	3
SCL-OF-30-2-SI-F-018	Silicone	30x10	2	5	12	3.5	12	22	G 1/8 inch (Female)	3
SCL-OF-36-2-SI-F-018	Silicone	36x12	2	5	12	4.5	12	22	G 1/8 inch (Female)	3
SCL-OF-15-1-SI-M-018	Silicone	15x5	1	5	9	2	12	26	G 1/8 inch (Male)	3
SCL-OF-18-1-SI-M-018	Silicone	18x6	1	5	9	2	12	26	G 1/8 inch (Male)	3
SCL-OF-24-1-SI-M-018	Silicone	24x8	1	5	12	3	12	26	G 1/8 inch (Male)	3
SCL-OF-30-2-SI-M-018	Silicone	30x10	2	5	12	3.5	12	26	G 1/8 inch (Male)	3
SCL-OF-36-2-SI-M-018	Silicone	36x12	2	5	12	4.5	12	26	G 1/8 inch (Male)	3
SCL-OF-15-1-SI-M-M5	Silicone	15x5	1	5	9	2	12	22	G M5 (Male)	2.4
SCL-OF-18-1-SI-M-M5	Silicone	18x6	1	5	9	2	12	22	G M5 (Male)	2.4
SCL-OF-24-1-SI-M-M5	Silicone	24x8	1	5	12	3	12	22	G M5 (Male)	2.4
SCL-OF-30-2-SI-M-M5	Silicone	30x10	2	5	12	3.5	12	22	G M5 (Male)	2.4
SCL-OF-36-2-SI-M-M5	Silicone	36x12	2	5	12	4.5	12	22	G M5 (Male)	2.4
SCL-OF-45-3-SI-F-014	Silicone	45x15	3	12	17	4	21	33	G 1/4 inch (Female)	6.5
SCL-OF-60-3-SI-F-014	Silicone	60x20	3	12	17	4	21	33	G 1/4 inch (Female)	6.5
SCL-OF-75-3-SI-F-014	Silicone	75x25	3	12	18	4	22	34	G 1/4 inch (Female)	6.5
SCL-OF-45-3-SI-M-014	Silicone	45x15	3	12	17	4	21	37	G 1/4 inch (Male)	6.5
SCL-OF-60-3-SI-M-014	Silicone	60x20	3	12	17	4	21	37	G 1/4 inch (Male)	6.5
SCL-OF-75-3-SI-M-014	Silicone	75x25	3	12	18	4	22	38	G 1/4 inch (Male)	6.5
SCL-OF-18-1-U-F-018	Polyurethane (PUR)	18x6	1	5	9	2	12	22	G 1/8 inch (Female)	3
SCL-OF-24-1-U-F-018	Polyurethane (PUR)	24x8	1	5	12	3	12	22	G 1/8 inch (Female)	3
SCL-OF-30-2-U-F-018	Polyurethane (PUR)	30x10	2	5	12	3.5	12	22	G 1/8 inch (Female)	3
SCL-OF-36-2-U-F-018	Polyurethane (PUR)	36x12	2	5	12	4.5	12	22	G 1/8 inch (Female)	3
SCL-OF-18-1-U-M-018	Polyurethane (PUR)	18x6	1	5	9	2	12	26	G 1/8 inch (Male)	3
SCL-OF-24-1-U-M-018	Polyurethane (PUR)	24x8	1	5	12	3	12	26	G 1/8 inch (Male)	3
SCL-OF-30-2-U-M-018	Polyurethane (PUR)	30x10	2	5	12	3.5	12	26	G 1/8 inch (Male)	3
SCL-OF-36-2-U-M-018	Polyurethane (PUR)	36x12	2	5	12	4.5	12	26	G 1/8 inch (Male)	3
SCL-OF-18-1-U-M-M5	Polyurethane (PUR)	18x6	1	5	9	2	12	22	G M5 (Male)	2.4
SCL-OF-24-1-U-M-M5	Polyurethane (PUR)	24x8	1	5	12	3	12	22	G M5 (Male)	2.4
SCL-OF-30-2-U-M-M5	Polyurethane (PUR)	30x10	2	5	12	3.5	12	22	G M5 (Male)	2.4
SCL-OF-36-2-U-M-M5	Polyurethane (PUR)	36x12	2	5	12	4.5	12	22	G M5 (Male)	2.4
SCL-OF-45-3-U-F-014	Polyurethane (PUR)	45x15	3	12	17	4	21	33	G 1/4 inch (Female)	6.5
SCL-OF-60-3-U-F-014	Polyurethane (PUR)	60x20	3	12	17	4	21	33	G 1/4 inch (Female)	6.5
SCL-OF-45-3-U-M-014	Polyurethane (PUR)	45x15	3	12	17	4	21	33	G 1/4 inch (Male)	6.5
SCL-OF-60-3-U-M-014	Polyurethane (PUR)	60x20	3	12	17	4	21	33	G 1/4 inch (Male)	6.5

Oval-bellows suction pads, 2.5-fold, 25 - 75 mm



Reference	Material	AxB (mm)	Stroke (mm)	D1 (mm)	D2 (mm)	D3 (mm)	h (mm)	H (mm)	Connection	DN	Suitable fitting
SCL-OB-25-6-N	NBR (nitrile rubber)	25x8	6	5	10	2.5	18.5	28.5			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OB-45-8P5-N	NBR (nitrile rubber)	45x15	8.5	12	17.5	5	28.5	40.5			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OB-75-10P5-N	NBR (nitrile rubber)	75x25	10.5	12	17.5	6	34.5	46.5			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OB-25-6-SI	Silicone	25x8	6	5	10	2.5	18.5	28.5			FL1-F-A-018G-3, FL1-M-A-018G-3, FL1-M-A-M5-2P4
SCL-OB-45-8P5-SI	Silicone	45x15	8.5	12	17.5	5	28.5	40.5			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OB-75-10P5-SI	Silicone	75x25	10.5	12	17.5	6	34.5	46.5			FL1-F-A-014G-6P5, FL1-M-A-014G-6P5
SCL-OB-25-6-N-F-018	NBR (nitrile rubber)	25x8	6	5	10	2.5	18.5	28.5	G 1/8 inch (Female)	3	
SCL-OB-25-6-N-M-018	NBR (nitrile rubber)	25x8	6	5	10	2.5	18.5	32.5	G 1/8 inch (Male)	3	
SCL-OB-25-6-N-M-M5	NBR (nitrile rubber)	25x8	6	5	10	2.5	18.5	28.5	G M5 (Male)	2.4	
SCL-OB-45-8P5-N-F-014	NBR (nitrile rubber)	45x15	8.5	12	17.5	5	28.5	40.5	G 1/4 inch (Female)	6.5	
SCL-OB-75-10P5-N-F-014	NBR (nitrile rubber)	75x25	10.5	12	17.5	6	34.5	46.5	G 1/4 inch (Female)	6.5	
SCL-OB-45-8P5-N-M-014	NBR (nitrile rubber)	45x15	8.5	12	17.5	5	28.5	44.5	G 1/4 inch (Male)	6.5	
SCL-OB-75-10P5-N-M-014	NBR (nitrile rubber)	75x25	10.5	12	17.5	6	34.5	50.5	G 1/4 inch (Male)	6.5	
SCL-OB-25-6-SI-F-018	Silicone	25x8	6	5	10	2.5	18.5	28.5	G 1/8 inch (Female)	3	
SCL-OB-25-6-SI-M-018	Silicone	25x8	6	5	10	2.5	18.5	32.5	G 1/8 inch (Male)	3	
SCL-OB-25-6-SI-M-M5	Silicone	25x8	6	5	10	2.5	18.5	28.5	G M5 (Male)	2.4	
SCL-OB-45-8P5-SI-F-014	Silicone	45x15	8.5	12	17.5	5	28.5	40.5	G 1/4 inch (Female)	6.5	
SCL-OB-75-10P5-SI-F-014	Silicone	75x25	10.5	12	17.5	6	34.5	46.5	G 1/4 inch (Female)	6.5	
SCL-OB-45-8P5-SI-M-014	Silicone	45x15	8.5	12	17.5	5	28.5	44.5	G 1/4 inch (Male)	6.5	
SCL-OB-75-10P5-SI-M-014	Silicone	75x25	10.5	12	17.5	6	34.5	50.5	G 1/4 inch (Male)	6.5	